



Home Generators

**RESV** Generators

10 and 12 kW



# Reliable Home Standby Power

Our 10- and 12-kW generators offer quiet, reliable performance in a compact footprint that provides maximum felxibility for installation on smaller lots.

### PowerBoost<sub>™</sub> Technology

Only Kohler has PowerBoost technology, which enables our 10- and 12-kW generators to accept heavy loads (like air conditioning or sump pump) without dropping power to other loads in your home. In addition, KOHLER® generators will have your home powered within ten seconds of an outage.

#### **Get Connected**

Get your generator Internet-connected to get peace of mind in the palm of your hand. Whether you're home or on the go, Kohler's mobile app will let you monitor your generator system anytime from anywhere and get instant updates via text or email.

### **Commercial-Grade KOHLER Engine**

Every KOHLER generator features a heavy-duty engine built to exceed the demands of standby power.

## **Premium Warranty**

You get our 2,000-Hour Five-Year Premium Limited Warranty, covering parts, labor, and dealer travel for the full warranty period. Optional extended warranties are also available.

## **Compact Footprints**

RESV generators offer smaller footprints and ample power for the necessities during an outage. They are also NFPA-37 compliant to have an 18-inch setback from any structure.

	10 kW	12 kW
Model Number	10RESV	12RESV
Rated Power LPG/NG	10/9	12/11
Voltage @ 60 Hz Single-Phase	120/240	120/240
Amps LPG/NG @ 240 V Single-Phase	41.7/37.5	50/45.8
Engine/Alternator RPM	3600	3600
Three-Phase Available	No	No
Engine	725 CC	725 CC
	21.4 HP	21.4 HP
	KOHLER 7000 Series OHV KT725	KOHLER 7000 Series OHV KT725
	V-Twin	V-Twin
	Solid Pushrods	Solid Pushrods
Peak Motor Starting kVA at 240 V (35% Dip for Lower Voltages)	16.8	16.8
Fuel	LPG/NG	LPG/NG
Engine Cooling	Air-Cooled	Air-Cooled
Fuel Pressure Requirement (in H20)	NG 3.5-11 LP 7-11	NG 3.5-11 LP 7-11
Enclosure	Powder-Coated Steel	Powder-Coated Steel
Single-Point Sound Output dBA at 23 Ft (During Exercise/ Normal Operation)*	64/69	64/69
Dimensions (Inches)	28 x 30 x 32	28 x 30 x 32
Digital Voltage Regulation	+/- 1.0%	+/- 1.0%
Excitation	PowerBoost-Brushed With Aux Winding	PowerBoost-Brushed With Aux Winding
Warranty	Five-Year Premium Limited	Five-Year Premium Limited
18-Inch Reduced Setback	Yes	Yes
Mossy Oak Patterns	No	No
Kohler Color Options	No	No

<sup>\*</sup>Single-point sound levels are the lowest of eight points measured around the generator. Sound levels are measured at the front of the generator. Actual sound levels may vary based on installation parameters.

