# **KOHLER**®



# *RCA Generators* 14 kW, 20 kW, 26 kW

Home Generators

# Reliable Home Standby Power

Our 14-, 20-, and 26-kW RCA generators offer quiet, reliable performance to power your home.

#### PowerBoost™ Technology

Only Kohler has PowerBoost™ technology which enables our RCA generators to accept heavy loads (like air conditioning or sump pump) without dropping power to other loads in your home. In addition, KOHLER® generators will have your home powered within 10 seconds of an outage.

# Commercial-Grade KOHLER Command PRO® Engine

Every KOHLER RCA generator features a heavyduty engine built to exceed the demands of standby power. The generators are built with hydraulic valve lifters to eliminate need for lengthy break-in periods and expensive valve adjustments.

#### **Easy to Install and Maintain**

A simple terminal block helps streamline installation. The RCA line of generators accommodates natural gas fuel pressure as low as 3.5 inches to eliminate expensive gas service upgrades.



## 26-kW Home Generator

**Toolless Access in 10 Seconds** 

The corrosion-resistant enclosure is designed

you have full access to key components for

is also NFPA 37-compliant to have an 18-inch

Connect your generator to the Internet to get

you're home or on the go, Kohler's mobile

peace of mind in the palm of your hand. Whether

You get our 2,000-hour, five-year premium limited

warranty, covering parts, labor, and dealer travel

for the full warranty period. Optional extended

app will let you monitor your generator system anytime from anywhere and get instant updates

setback from any structure.

**Get Connected** 

**Premium Warranty** 

warranties are also available.

via text or email.

to reduce time required to service the generator.

Once the lid is unlocked, in less than 10 seconds

scheduled maintenance or service. The enclosure

Introducing the KOHLER® 26-kW generator—the quietest, most durable, and most powerful air-cooled generator on the market.

#### **Ultra Quiet**

✓ The 26 RCA exercises at the volume of a conversation (56 dBA)—perfect for areas with stringent sound requirements.

#### Most Powerful\*

✓ In addition to featuring PowerBoost technology, it is rated at 109 Amps (LP) to power more in your home.

#### **Exceptionally Durable**

The 26 RCA includes oil-level and oil-pressure sensors to protect your engine if your generator needs to be left unattended during extended power outages.

# KOHLER.

#### Blend in or Stand out.

Customize your generator with ten new colors and three camouflage patterns. KOHLER® 14- to 26-kW kW RCA generators can now match your style to complement the color of your home or stand out to make a statement—only available with Kohler.



Cashmere
Cashmere standard color



KOHLER.



e KOHLER



Nevergreen

French Linen Gray

Pegasus

Pigeon Feather

eather Dover Gray











Royal Plum

Royal Hunter Green

Admiralty

Canyon Blue

Brick Dust

### KOHLER. × MOSSY OAK.



Mossy Oak® Break-Up Country®





Mossy Oak® Original Bottomland®

Mossy Oak® Shadow Grass® Habitat™

Mossy Oak is a trademark used under license from Haas Outdoors, Inc., by Kohler

# The Power of *Reliability*







	14 kW	20 kW	26 kW
Model Number	14RCA	20RCA	26RCA
Rated Power LPG/NG	14/12	20/18	26/24
Voltage @ 60 Hz Single-Phase	120/240	120/240	120/240
Amps LPG/NG @ 240 V Single-Phase	58/50	83/75	109/100
Engine/Alternator RPM	3600	3600	3600
Three-Phase Available	Yes	Yes	Yes
Engine	725 CC	999 CC	999 CC
	23.6 HP	30.9 HP	36.4 HP
	KOHLER Command PRO OHV CH740	KOHLER Command PRO OHV CH1000	KOHLER Command PRO OHV CH1006
	V-Twin	V-Twin	V-Twin
	Hydraulic Valve Lifters	Hydraulic Valve Lifters	Hydraulic Valve Lifters
Peak Motor Starting kVA at 240 V (35% Dip for Lower Voltages)	33	41	39
Fuel	LPG/NG	LPG/NG	LPG/NG
Engine Cooling	Air-Cooled	Air-Cooled	Air-Cooled
Fuel Pressure Requirement (in H2O)	NG 5-11 LP 7-11	NG 3.5-11 LP 7-11	NG 3.5-11 LP 7-11
Enclosure	Powder-Coated Corrosion- Resistant Aluminum	Powder-Coated Corrosion- Resistant Aluminum	Powder-Coated Corrosion- Resistant Aluminum
Single-Point Sound Output dBA at 23 Ft (During Exercise/ Normal Operation)*	58/63	62/67	56/67
Dimensions (inches)	47 x 26 x 32	47 x 26 x 32	47 x 26 x32
Digital Voltage Regulation	+/- 1.0%	+/- 1.0%	+/- 1.0%
Excitation	PowerBoost Brushed With Aux Winding	PowerBoost Brushed With Aux Winding	PowerBoost Brushed With Aux Winding
Warranty⁺	5-Year Premium Limited	5-Year Premium Limited	5-Year Premium Limited

<sup>\*</sup>Single-point sound levels are the lowest of eight points measured around the generator. RCA sound levels are measured at the front of the generator. Actual sound levels may vary based on installation parameters.

For more information, contact your Kohler source of supply, or call toll-free in the U.S. and Canada 1-800-544-2444





 $<sup>^{\</sup>dagger}18$  month or 1,000-hour warranty offered on nonstandby (off-grid) applications.