

**KOHLER® ×
MOSSY OAK®**



| Home Generators

Camouflage
patterns



Take your generator to the next level with Mossy Oak® camouflage patterns—exclusively from Kohler. Available in three unique designs, KOHLER® generators (14–26RCA) can now blend in perfectly with your existing landscaping. Or stand out to make a statement.

Camo patterns, tailored to your style—only from Kohler.



Mossy Oak Break-Up Country®



Mossy Oak Original Bottomland®



Mossy Oak Shadow Grass® Habitat™

	14 kW	20 kW	26 kW
Model Number	14RCA	20RCA	26RCA
Rated Power LPG (Liquid Propane)/ NG (Natural Gas) (kW)	14/12	20/18	26/24
Voltage @ 60 Hz Single-Phase	120/240		
Amps LPG/NG @ 240 V Single-Phase	58/50	83/75	109/100
Engine/Alternator RPM	3600		
Three-Phase Available	Yes		
Engine: KOHLER Command PRO CH740	725 cc	999 cc	
	23.6 hp	30.9 hp	36.4 hp
	KOHLER Command PRO OHV CH740	KOHLER Command PRO OHV CH1000	KOHLER Command PRO OHV CH1006
	V-TWIN		
	Hydraulic Valve Lifters		
Peak Motor Starting kVA at 240 V (35% Dip for Lower Voltages)	33	41	39
Fuel	LPG/NG		
Fuel Pressure Requirement (in H2O)	NG 5-11/LP 7-11	NG 3.5-11/LP 7-11	NG 3.5-11/LP 7-11
Excitation	Power Boost Brushed With Auxiliary Winding		
18-Inch Reduced Setback	Yes		
Engine Cooling	Air-Cooled		
Enclosure	Powder-Coated Corrosion-Resistant Aluminum		
Single-Point Sound Output dBA at 23 Feet (During Exercise/Normal Operation)†	58/63	62/67	56/67
Dimensions (L x W x H) Inches	47 x 26 x 32		
Digital Voltage Regulation	+/- 1.0%		
Warranty	5-Year Premium Limited†		

*Based on generator and load size.

†Lowest of 8 points around the generator as compared to competitor ratings. Sound levels at other points around generator may vary depending on installation parameters. Eighteen-month or 1000-hour warranty nonstandby (off-grid) applications.

KOHLERGenerators.com

KOHLER × MOSSY OAK®

PRINTED IN U.S.A. WF353902 G12-557 08/23 © KOHLER CO.