



REV	DATE	CHANGE NUMBER	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY
-	03NOV2020	CT207992	NEW DRAWING	AZE

UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: X.XX ± 0.25 X.X ± 1.0 X ± 1.5 ANGLES ± 0°30'				SURFACE FINISH MAX.	
THIRD ANGLE PROJECTION					
					
MAJOR				0 =	0
CRITICAL				0 =	0
CHARACTERISTICS COMPLY WITH KPS-80022					
DRAWN BY		AZE		DATE:	
APPROVED BY		KJB		03NOV2020	

DO NOT SCALE. THIS ASSEMBLY OR PART MUST COMPLY WITH PEP-RML-001. REFERENCE CAD MODEL FOR UNSPECIFIED DIMENSIONS.		
KOHLER. KOHLER, WISCONSIN 53044		
SCALE: NA	SHEET SIZE: B	SHEET 2 OF 4
TITLE: DIMENSION PRINT, 20RESC		
DWG NO.: ADV-9743		



NOTE:

1 THE RECOMMENDED DISTANCE FROM A STRUCTURE IS DEPENDENT ON STATE AND LOCAL CODES. NFPA 37, STANDARDS FOR THE INSTALLATION AND USE OF STATIONARY COMBUSTION ENGINES AND GAS TURBINES, STATES THIS DISTANCE SHOULD BE AT LEAST 5 FEET FROM A COMBUSTIBLE MATERIAL.

2 FOR INSTALLATIONS NEAR NON-COMBUSTIBLE STRUCTURE, A MINIMUM DISTANCE OF 18" IS REQUIRED TO ENSURE PROPER GENERATOR COOLING.

- ACCEPTABLE
- 1) EXHAUST IS AIMED AWAY OR PARALLEL TO STRUCTURE.
 - 2) EXHAUST IS NOT DIRECTED AT PLAY AREAS, PATIOS OR OTHER AREAS WHERE PEOPLE CONGREGATE.
 - 3) THE NEAREST WINDOW, VENT, DOOR OR SIMILAR STRUCTURE OPENING IS AT LEAST 5 FEET FROM THE EXHAUST END OF THE SET.
 - 4) SET HAS PROPER OFFSET FROM STRUCTURE.
 - 5) WINDOWS & DOORS ON ADJACENT WALLS ARE CLOSED.
 - 6) FURNACE AND OTHER SIMILAR INTAKES ARE AT LEAST 10 FEET FROM EXHAUST END OF SET.
 - 7) WEED BARRIER AND 3 INCH THICK GRAVEL BASE OR CONCRETE PAD LOCATED TO PREVENT GRASS & WEEDS FROM GROWING TOO CLOSE TO THE SET.
 - 8) NO PLANTS, SHRUBS OR OTHER COMBUSTIBLES ALLOWED IN CLEARANCE AREA. (MINIMUM 4 FT. FROM EXHAUST END).
 - 9) REFER TO OWNERS MANUAL FOR OTHER INSTALLATION CONSTRAINTS.
 - 10) NO PLANTS, SHRUBS, OR OTHER COMBUSTIBLES ALLOWED WITHIN 18" OF AIR INTAKE.

REV	DATE	CHANGE NUMBER	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL □ INDICATES PART NUMBERS AFFECTED BY LATEST DRAWING REVISION	BY
-	03NOV2020	CT207992	NEW DRAWING	AZE

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS IN MILLIMETERS
GENERAL TOLERANCES:
X.XX ± 0.25
X.X ± 1.0
X ± 1.5
ANGLES ± 0°30'
SURFACE FINISH
MAX.
THIRD ANGLE PROJECTION
MAJOR ♂ = 0
CRITICAL ♀ = 0
CHARACTERISTICS COMPLY WITH
KPS-80022
DRAWN BY AZE
DATE: 03NOV2020
APPROVED BY KJB

DO NOT SCALE.
THIS ASSEMBLY OR PART MUST
COMPLY WITH PEP-RML-001.
REFERENCE CAD MODEL FOR
UNSPECIFIED DIMENSIONS.
KOHLER.
KOHLER, WISCONSIN 53044
SCALE: NA SHEET SIZE: B SHEET 3 OF 4
TITLE:
DIMENSION PRINT, 20RESC
DWG NO.: **ADV-9743**

