

Model: KG80R

Multi- Fuel LPG/Natural Gas





The Kohler® Advantage

High Quality Power

Kohler generators provide advanced voltage and frequency regulation along with ultra-low levels of harmonic distortion for excellent generator power quality to protect your valuable electronics.

Fast Response

Kohler's Fast-Response[®] X excitation system delivers excellent voltage response and short-circuit capability Using a rare-earth permanent magnet (PM)-excited alternator.

• Extraordinary Reliability

Kohler is known for extraordinary reliability and performance and backs that up with a 5- year/2000- hour basic warranty.

Quiet Operation

Kohler home generators provide quiet, neighborhood friendly performance.

Standard Features

- Kohler Co. provides one-source responsibility for the generating system and accessories.
- The generator set and its components are prototype-tested, factory-built, and production-tested.
- The 60 Hz generator set meets NFPA 110, Level 2, when equipped with the necessary accessories and installed per NFPA standards.
- The generator set accepts rated load in one step.
- A standard 5 year/2000-hour basic warranty covers all systems and components.
- Quick-ship (QS) models with selected features are available. See your Kohler dealer for details.
- Kohler® APM402 controller. See controller features on page 3.
- The electronic, isochronous governor incorporates an integrated drive-by-wire throttle body actuator delivering precise frequency regulation.
- Engine Features:
 - Powerful and reliable Kohler 6.2 L Turbo charged liquid-cooled engine
 - Electronic engine management system
 - Simple field conversion between natural gas and LP vapor fuels while maintaining emission certification
- Approved for stationary standby applications in locations served by a reliable utility source.
- Certifications:
 - The 60 Hz generator set engine is certified by the Environmental Protection Agency (EPA) to conform to the New Source Performance Standard (NSPS) for stationary spark-ignited emissions.
 - o cUL/UL 2200 listed and CSA certified.
 - Accepted by the Massachusetts Board of Registration of Plumbers and Gas Fitters.

Generator Set Ratings

				Natural Gas Standby Rating		LP Gas Standby Rating		Line Circuit Breaker
Alternator	Voltage	Ph	Hz	kW/kVA	Amps	kW/kVA	Amps	Amps
	120/208	3	60	80/100	278	80/100	278	300
	127/220*	3	60	80/100	263	80/100	263	-
	120/240	3	60	80/100	241	80/100	241	250
4R9X	120/240*	1	60	77/77	321	77/77	321	-
	139/240*	3	60	80/100	241	80/100	241	-
	220/380*	3	60	80/100	152	80/100	152	-
	270/480	3	60	80/100	121	80/100	121	125
4T9X	120/240	1	60	80/80	334	80/80	334	350

^{*} Voltage configuration not available from the factory. Field- adjustable by an authorized service technician.

RATINGS: All three-phase units are rated at 0.8 power factor. All single-phase units are rated at 1.0 power factor. Standby Ratings: The standby rating is applicable to varying loads for the duration of a power outage. There is no overload capability for this rating. Ratings are in accordance with ISO-8528-1 and ISO-3046-1. Obtain technical information bulletin (TIB-101) for ratings guidelines, complete ratings definitions, and site condition derates. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever. For dual fuel engines, use the natural gas ratings for both the primary and secondary fuels.

Alternator Specifications

Specifications	S	Alternator
Manufacturer		Kohler
Type		4-Pole, Rotating-Field
Exciter type		Brushless, Rare-Earth
		Permanent Magnet
Leads: quantity	y, type	
4RX		12, Reconnectable
4TX		4, 120/240 V
Voltage regula	tor	Solid State, Volts/Hz
Insulation:		NEMA MG1
Material		Class H
Temperatu	ıre rise	130°C, Standby
Bearing: quant	tity, type	1, Sealed
Coupling		Flexible Disc
Amortisseur windings		Full
Voltage regula	tion, no-load to full-load	±0.5%
One-step load	acceptance	100% of Rating
Unbalanced lo	ad capability	100% of Rated Standby
		Current
Peak motor sta	arting kVA:	(35% dip for voltages below)
480 V	4R9X (12 lead)	385 (60 Hz)
240 V	4T9X (4 lead)	237 (60 Hz)
	•	

- The unique Fast-Response[®] X excitation system delivers excellent voltage response and short-circuit capability using a rare-earth, permanent magnet (PM)-excited alternator.
- Brushless, rotating-field alternator.
- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting.
- Sustained short-circuit current of up to 300% of the rated current for up to 10 seconds.
- Sustained short-circuit current enabling downstream circuit breakers to trip without collapsing the alternator field.
- Self-ventilated and dripproof construction.
- Superior voltage waveform from a two-thirds pitch stator and skewed rotor.
- Windings are vacuum-impregnated with epoxy varnish for dependability and long life.
- Total harmonic distortion (THD) from no load to full load with a linear load is less than 3.2%.

Application Data

Engine

Engine Specifications	60 Hz
Manufacturer	Kohler
Engine: model, type	KG6208TSD 6.2 L
	Turbocharged, Aftercooled
	KG6208TSC* 6.2 L
	Turbocharged, Aftercooled
Cylinder arrangement	V-8
Displacement, L (cu. in.)	6.2 (378)
Bore and stroke, mm (in.)	101.6 x 95.25 (4.00 x 3.75)
Compression ratio	9.8:1
Rated rpm	1800
Max. power at rated rpm, kW (HP)	
Natural Gas	93.6 (126)
LPG	94.6 (127)
Cylinder head material	Cast Aluminum
Piston type and material	Cast Aluminum
Crankshaft material	Cast Iron
Valve (exhaust) material	Forged Steel
Governor type	Electronic
Frequency regulation, no-load to full-load	Isochronous
Frequency regulation, steady state	±1.0%
Frequency	Fixed
Air cleaner type, all models	Dry
* KG6208TSC includes catalyst (60 Hz	only)

KG6208TSC includes catalyst (60 Hz only).

Exhaust

Exhaust System	60 Hz
Exhaust manifold type	Dry
Exhaust flow at rated kW, m ³ /min. (cfm)	18 (636)
Exhaust temperature at rated kW, dry exhaust, °C (°F)	715 (1319)
Maximum allowable back pressure, kPa (in. Hg)	12 5 (3.7)
Exhaust outlet size at engine hookup, mm (in.)	88.9 (3.5)

Engine Electrical

g		
Engine Electrical System	60 Hz	
Ignition system	Coil Pack	
Battery charging alternator:		
Ground (negative/positive)	Negative	
Volts (DC)	12	
Ampere rating	130	
Starter motor rated voltage (DC)	12	
Battery, recommended cold cranking amps (CCA):		
Qty., rating for - 18°C (0°F)	One, 650	
Battery voltage (DC)	12	

Fuel

Fuel System	60	Hz
Fuel type		s, LP Gas, or I Fuel
Fuel supply line inlet	1.25	NPT
Natural gas and LPG vapor fuel supply pressure, kPa (in. H ₂ O)	1.74-2.	74 (7-11)
Fuel Composition Limits *	Nat. Gas	LP Gas
Methane, % by volume	90 min.	_
Ethane, % by volume	4.0 max.	_
Propane, % by volume	1.0 max.	85 min.
Propene, % by volume	0.1 max.	5.0 max.
C ₄ and higher, % by volume	0.3 max.	2.5 max.
Sulfur, ppm mass	25 ו	max.
Lower heating value, MJ/m ³ (Btu/ft ³), min.	33.2 (890)	84.2 (2260)

^{*} Fuels with other compositions may be acceptable. If your fuel is outside the listed specifications, contact your local distributor for further analysis and advice.

Lubrication

Lubricating System	60 Hz
Туре	Full Pressure
Oil pan capacity, L (qt.)	5.7 (6.0)
Oil pan capacity with filter and oil cooler, L (qt.)	8.0 (8.5)
Oil filter: quantity, type §	1, Cartridge
Kohler recommends the use of Kohler Ge	nuine oil and filters

Cooling

60 Hz
45 (113)
7.3 (1.93)
22.7 (6.0)
112.5 (29.7)
66.5 (3785)
9 (512)
Centrifugal
711 (28)
7.0 (9.4)
0.12 (0.5)

Operation Requirements

60 Hz
230 (8122)
5.3 (187)
24 (1366)
8.8 (500)

Fuel Consumption ‡	60 Hz
Natural Gas, m ³ /hr. (cfh) at % load	Standby Ratings
100%	34.0 (1202)
75%	29.2 (1032)
50%	22.7 (803)
25%	14.9 (527)


LP Gas, m ³ /hr. (cfh) at % load	Standby Ratings
100%	14.7 (521)
75%	11.7 (413)
50%	7.7 (272)
25%	5.2 (183)

‡ Nominal fuel rating: Natural gas, 37 MJ/m³ (1000 Btu/ft.³) LP vapor, 93 MJ/m³ (2500 Btu/ft.³)

LP vapor conversion factors:

8.58 ft.³ = 1 lb. 0.535 m³ = 1 kg. 36.39 ft.³ = 1 gal.

Controllers



APM402 Controller


Provides advanced control, system monitoring, and system diagnostics for optimum performance and compatibility.

- Digital display and menu control provide easy local data access
- Measurements are selectable in metric or English units
- Remote communication thru a PC via network or serial configuration
- Controller supports Modbus® protocol
- Integrated hybrid voltage regulator with ±0.5% regulation
- Built-in alternator thermal overload protection
- NFPA 110 Level 2 capability

Refer to G6-161 for additional controller features and accessories.

 $\mathsf{Modbus}^{\texttt{®}}$ is a registered trademark of Schneider Electric.

Sound Enclosure



- Model KG80R sound levels are 67 dB(A) during normal operation*.
- All sound levels are measured at a distance of 23 ft. (7 m) from the generator set.
- Sound attenuating enclosure uses acoustic insulation that meets
 UL 94 HF1 flammability classification and repels moisture absorption.
- Vertical air inlet and outlet discharge with 90 degree bends to redirect air and reduce noise.
- Internal-mounted critical silencer and flexible exhaust connector.
- Skid-mounted, steel (standard) or aluminum (optional) construction with hinged doors.
- Fade-, scratch-, and corrosion-resistant Kohler® Cashmere Power Armor™ textured e-coat paint.
- Lockable, flush-mounted door latches.
- Certified to withstand 299 kph (186 mph) wind load rating (aluminum enclosures only).
- * Lowest of 8 points measured around the generator. Sound levels at other points around generator may be higher depending on installation parameters.



KOHLER CO., Kohler, Wisconsin 53044 USA Phone 920-457-4441, Fax 920-459-1646 For the nearest sales and service outlet in the US and Canada, phone 1-800-544-2444 KOHLERPower.com

Standard Features

- Air Cleaner Restriction Indicator
- Alternator Protection
- Battery Rack and Cables
- Battery Charger, 12 V, 6 A
- Block Heater, 1500 W
- cUL/UL 2200 Listed, CSA Certified
- Electronic, Isochronous Governor
- Engine Fluids Added(Oil & Coolant)
- Flexible Fuel Line (for fuel supply connection)
- Gas Fuel System (includes fuel mixer, electronic secondary gas regulator, gas solenoid valve, and flexible fuel line between the engine and the skid-mounted fuel system components)
- Integral Vibration Isolation
- Line Circuit Breaker, Thermal Magnetic, 80% Rated, 3 Pole
- Local Emergency Stop Switch
- Oil Drain Extension
- Operation and Installation Literature
- Rodent Guards
- Secondary Gas Solenoid Valve
- Steel Sound Enclosure
- 5 year/2000 Hour Basic Warranty

Available Options

•
Approvals and Listings Exhaust catalyst* QS Factory installed only
Enclosure Aluminum Sound Enclosure
Fuel System Dual Fuel NG/LPG (automatic changeover)*QS factory installed only.
Controller Remote Emergency Stop Run Relay Remote Annunciator panel Two Input/Five Output Module
Automotic Transfer Switches and Assessation

ries
ĺ

☐ For larger than 400 A or 3 phase, KEP Service Entrance Rated Automatic Transfer Switch option is available

For larger than 400 A or 3 phase, KSS Standard Automatic Transfer Switch option is available

Load shed kit for RDT

Model RDT Automatic Transfer switch

 Power relay modules (use up to 4 relay modules for each load management device)

Electrical System

Alternator Strip Heater

Battery

Battery Heater

Literature

☐ General Maintenance

Overhaul

Production

Warranty

5-Year Premium Limited Warranty


Dimensions and Weights


Overall Size, L x W x H, mm (in.) :

3525 x 1154 x 1665 (138.8 x 45.4 x 65.5)

Weight, wet, kg (lb.): With steel sound enclosure With aluminum sound enclosure

1427 (3146) 1337 (2948)





NOTE: This drawing is provided for reference only and should not be used for planning installation. Contact your local dealer for more detailed information.

DISTRIBUTED BY: